

Conductive Biosensor Ink



IGSB04192 Technical Data Sheet



Creating Material Change
www.haydale.com  HaydaleGraphene
T: +44(0)1269 842946 E: info@haydale.com

Screen Printable Biosensor Graphene Ink

Product name:	IGSB04192
Synonyms:	Biosensor Ink, Graphene Ink
Chemical family:	Functional Graphene Ink
Properties:	Electrically Conductive, Flexible, Stable, Inert, Environmentally Friendly, No Metals, Robust, Ease of Printing
Typical uses:	Uric Acid Biosensors, Printed Electrodes, Plastic Electronics, Sensors

Key Features


- Lower viscosity ink optimised for uric acid sensitivity
- Contains functionalised HDPlas® materials
- Designed for large volume screen printing
- Electrically conductive, boosted by specific functional groups
- Carbon, organic solvent-based ink (no metal)
- Curable at low temperatures
- Can be applied to a variety of surfaces
- Flexible on appropriate substrate
- Customisable
- Good shelf-life

Handling Guidelines

- Printing equipment: screen printer; semi-automatic, manual, fully-automatic and reel to reel
- $<20 \Omega/\text{sq}$ normalised to 25 microns (μm), screen printed on stainless steel screen, mesh size 230, angle 45, thickness 30 microns, emulsion E04, tension 28N, raw mesh 77
- Substrates including but not limited to PET and TPU
- Drying conditions: can be dried at 120°C for 5 minutes; infrared drying can be used in conjunction with conventional heated dryers
- Clean-up solvent IMC00001 on press wash and mesh opener. Warning, do not use other screen cleaners as this may result in the ink gelling and the mesh blocking prematurely
- Storage: when not in use, the product should be kept sealed in its container and stored at controlled temperatures between $7\text{-}20^\circ\text{C}$
- Warning, do not allow to freeze
- Shelf-life: ink in an unopened container has a recommended shelf-life of 6 months from date of delivery. Stir well before use

Test	Specification
Viscosity - Malvern Rheometer -25°C at Sheer Rate 300 s^{-1}	$<5 \text{ Pa}\cdot\text{s}$
Thickness - Micrometer	Typical 13 micron wet emulsion; 7 micron dried
Solids Content - Loss on Drying	37 - 41%
Fineness of Grind - Hegman Gauge	First Streak $< 20 \mu\text{m}$
Sheet Resistivity - 4-Point Probe	$<20 \Omega/\text{sq}$ normalised to $25 \mu\text{m}$
Linear Sweep Voltammetry - EmStat Potentiometer	350 – 400 mV Peak
Coverage	$984\text{cm}^2/\text{g}$ single pass
Adhesion	ASTM rating 5B when printed on PET and TPU
Pencil Hardness	Typical 3H when printed on PET and TPU

Linear Sweep Voltammetry



IGSB04192 – Linear sweep voltammogram 0.5 mM uric acid in basic aqueous solution.

Contact us: **T:** +44(0)1269 842946 **E:** info@haydale.com



The content supplied in this sheet ("Information") supersedes all previous versions supplied. Version 1, October 2021

The Information should be used solely as guidance for the safe handling, storage, processing and/or use of the Product and is only typical of the methods described. The Haydale Group (Haydale Group means Haydale Limited, as a subsidiary of Haydale Graphene Industries plc., and any subsidiary or holding company from time to time and any subsidiary from time to time of any holding company of Haydale Limited) gives no express or implied warranty or guarantee or representation as to the behaviour of the Product described herein during any handling or storage or processing or use of the Product. To the extent permissible by law the Haydale Group shall under no circumstances whatever be liable whether in contract, tort (including negligence), breach of statutory duty, or otherwise, for any damage, including loss of profit, or any indirect or consequential loss arising under or in connection with any handling or storage or processing or use of the Product.